



presto Silicone Spray

Ord.-no.: 306345, 429774, 540646

Technical Information



presto Silicone Spray is a high-quality lubricant for lubricating and protecting synthetic materials without leaving and marks. Maintains plastic surfaces free of stains. It is particularly suited to isolation when a flexible protective film is needed. Application areas: - Protecting for electronic contact from moisture and corrosion - Lubricating seat rails, head rests and sunroofs - Keeping door rubbers flexible - On cold and warm water valves in heating systems and sanitary facilities

Quality & properties

- Antistatic effect
- Impregnating effect
- Prevents freezing and drying out of rubber parts as well as plastic parts from squeaking
- Resistant to weather conditions
- Operating temperature between -50°C and +200°C
- Water repellent
- Excellent corrosion protection
- No resinifying or coking
- Not poisonous
- Excellent mechanical and thermo stability

Physical & chemical data

- Base: Polydimethylsiloxane
- Colourname: transparent
- Smell: Characteristic
- Surfaces: synthetic materials
- Minimum Working Temperature: 5 °C
- Maximum Working Temperature: 30 °C
- Dielectric strength: 14 kv/mm
- Refractive index: 1.403
- Vapour pressure: 3500/20 bar
- Relative density: 0.72 g/ml
- Storage stability: 10 y
- Content:
 - ◊ 400 ML
 - ◊ 150 ML

How to use

- Bring the can to room temperature.
- Operating temperature 5° to 30°C.
- Shake can for 2 minutes before use.
- Surface should be clean, dry and free of grease.
- Cover coated or plastic parts with masking tape.
- According to condition and size, apply fine, even coats to the parts to be treated e.g. ca. 5 cm for door rubber or up to ca. 20 cm for a cabrio roof.
- For treatment of plastic parts and rubber, flash off for ca. 5 minutes and then rub with a soft cloth.
- Do not use on dashboard, wheel running surface, steering wheel and pedals!

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labeling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +49 (0) 62 66 75-266 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of August 18, 2022 – This release replaces all eventually earlier issued versions.

